


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY
DIMENSIONS ARE IN mm [INCHES]

| | |
|----------------------------|-------------|
| EXPANSION POWER | 3X |
| DESIGN WAVELENGTH | 510 - 555nm |
| CENTER WAVELENGTH | 532 ± 1nm |
| ENTRANCE BEAM MAX DIAMETER | 10.00mm |
| INPUT APERTURE DIAMETER | 11.00mm |

EO® Edmund Optics

| | | | |
|--------|---|-----|----|
| TITLE | 3X, 532nm Draconis™ Nd:YAG Laser Line Beam Expander | | |
| DWG NO | 59125 | REV | 00 |