


A



Ø 35mm  
[1.378in]

32mm  
[1.26in]

A

10mm MAX THICKNESS OF OPTIC  
[.394in MAX]

2X 8mm  
[.315in]

2mm  
[.079in]

Ø 9mm  
[.354in]  
CLEAR APERTURE

Ø 12.3mm  
[.484in]  
DIAMETER OF OPTIC

M6 x 1  
x 5.5mm [.22in] DEEP

CELL

SECTION A-A

16mm  
[.63in]

14mm  
[.551in]

1/4-20 UNC  
x 5.5mm [.22in] DEEP

RETAINER

M13 x 0.75

12mm  
[.472in]

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY  
DIMENSIONS ARE IN mm [INCHES]



Edmund Optics®

TITLE	Optic Mount, 12.0mm Optic Diameter, 10mm Max Optic Thickness		
DWG NO	64555	MATERIAL	BLACK ANODIZED ALUMINUM
			SHEET 1 OF 1