



TECHSPEC® Negative Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® NEGATIVE ACHROMATIC LENSES




45421
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 1.386
GD RADIUS : 2.695
SCALE BAR : 10

REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

45421
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 113.6046 μm
DIFFRACTION LIMITED RANGE: 37.509 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



TRANSVERSE RAY FAN PLOT


45421
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 50.000 \mu\text{m}$.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

45421
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



EO Edmund
optics | worldwide

www.edmundoptics.com