



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES




47643
TUE DEC 16 2008 UNITS ARE μm .
FIELD : 1
RMS RADIUS : 4.957
GD RADIUS : 11.262
SCALE BAR : 40

REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

47643
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 430.4067 μm
DIFFRACTION LIMITED RANGE: 84.604 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



47643
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

47643
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

EO Edmund
optics | worldwide

www.edmundoptics.com