


TECHSPEC® Achromatic Lenses


Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



+ 0.4861
x 0.5876
■ 0.6563



SURFACE: INA

IPA: 0.000 MM


47713
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 166.819
GD RADIUS : 412.821
SCALE BAR : 1000

REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47713
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 263.2652 μm
DIFFRACTION LIMITED RANGE: 6.698 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)




47713
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 1000.000 \mu\text{m}$.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47713
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF



EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

EO Edmund
optics | worldwide

www.edmundoptics.com