




NOTES:

- 1. SUBSTRATE:
BOROFLOAT®
- 2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)
T(AVG) <1.0% @ 535 - 565nm
T(AVG) >80% @ 380 - 470nm
T(AVG) >80% @ 655 - 750nm

3. FINE GROUND SURFACE

- 4. ROHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	≥85%	≥85%
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 Edmund Optics®			
TITLE	12.5mm Diameter, Magenta Dichroic Filter		
DWG NO	52539	SHEET 1 OF 1	