




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



REV. A	VALUE
SHAPE	PLANO
TRANSMISSION WAVELENGTH	439 - 647.1
DURABILITY	MIL-C-48497A
CUT-ON WAVELENGTH	427
SURFACE FLATNESS	>95
SURFACE QUALITY	60-40
CLEAR APERTURE	Ø8.8
BEVEL	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



TITLE

Ø12.5mm, 427nm, DICHROIC LASER BEAM
COMBINER

ALL DIMS IN

mm

DWG NO

86382

SHEET
1 OF 1