NOTES:

1. SUBSTRATE MATERIAL: N-BK7

2. ROHS COMPLIANT


3. SURFACE \$1 TO BE PARALLEL WITH SURFACE \$2 TO WITHIN ≤ 3 ARCMIN

4. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 60% R ±5% @ 550nm 40% T ±5% @ 550nm

S2: AR R(avg) ≤1%, R(abs) ≤2% @ 400 - 700nm

5. CUT WITH 0.25mm MAXIMUM EDGE CHIP



FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	<u></u>	20	7		Edmund Op	tics®
REV. A	51	S2				
SHAPE	PLANO	PLANO				
ANGLE OF INCIDENCE	45°	45°	THIRD ANGLE		Ø25mm, 40 R/60 T, PLATE BEAMSPLITTER	
SURFACE QUALITY	60-40	60-40				0.1557
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm	ALL DIMS IN mm	DWG NO	68403	SHEET 1 OF 1