

NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <30 arcsec
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: RAVG ≤0.4% @ 425 - 675nm



5. Rohs Compliant







PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	20-10
WAVELENGTH RANGE	425 - 675nm	425 - 675nm
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

			Edmund Option	S®
THIRD ANGLE PROJECTION		TITLE	10mm DIAMETER VIS 0° COATED, ULTRA N-BK7 WINDOW	A-THIN
ALL DIMS IN	mm	DWG NO	83100	SHEET 1 OF 1