




NOTES:

1. SUBSTRATE MATERIAL: N-BK7
2. ROHS COMPLIANT
3. COATING (APPLY ACROSS CLEAR APERTURE)
 S1: Ravg >98% @ 400 - 750nm
 S2: NONE

4. FINE GRIND SURFACE




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A | S1 | S2 |
|---------------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| ANGLE TOL. (arcmin) | ±2 | ±2 |
| SURFACE QUALITY | 40-20 | 40-20 |
| SURFACE FLATNESS | λ/8 | λ/8 |
| CLEAR APERTURE | 90% | 90% |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE PROJECTION



ALL DIMS IN

mm



| TITLE | DWG NO | SHEET |
|---|--------|--------|
| 15mm, 400 - 750nm DIELECTRIC COATED, N-BK7 RIGHT ANGLE MIRROR | 87389 | 1 OF 1 |