



1. SUBSTRATE MATERIAL:
N-BK7



- S1 & S2: VIS 0° (425-675nm)
R(AVG) ≤ 0.4% @ 425 - 675nm

4. RoHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	100.00			
SHAPE	CONVEX	PLANO	BFL	98.66			
RADIUS	51.68	INFINITY		TITLE		12.5mm H X 25mm L X 100mm FL VIS 0° COATED, CYLINDER LENS	
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	11.50 x 24.00	11.50 x 24.00					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					
			ALL DIMS IN	mm	DWG NO	69725	SHEET 1 OF 1