

NOTES:

1. SUBSTRATE MATERIAL:
N-BK7



2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Gold
R(avg) >96% @ 700 - 2000
R(avg) >96% @ 2000 - 10000nm

S2: NONE

 3. FINE GROUND SURFACE

4. RoHS COMPLIANT




SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	CONCAVE	CONVEX
RADIUS	30mm	30mm
APERTURE	f/0.43	N/A
EFFECTIVE FOCAL LENGTH	15mm	N/A
FOCAL LENGTH TOLERANCE	±2%	N/A
SURFACE QUALITY	80-50	N/A

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm

 **Edmund Optics®**

TITLE

35mm Dia. x 15mm FL Protected Gold,
Concave Mirror

DWG NO

43837

SHEET
1 OF 1