

NOTES:


1. COATING (APPLY ACROSS CLEAR APERTURE)


S1: R(abs) 50% ±5% @ 550nm R(abs) 50% ±10% @ 400 - 700 nm T(abs) 50% ±5% @ 550nm T(abs) 50% ±10%@ 400 - 700nm FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



S2: R(avg) <1.0% @ 400 - 700nm R(abs) <2.0% @400 - 700nm







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2	THIRD ANGLE PROJECTION	TITLE	50R/50T, VIS, C-MOUNTED PLATE BEAMSPLITTER	
SURFACE QUALITY	60-40	60-40			DEAMOI LITTER	CLIEFT
SURFACE FLATNESS	1λ	1λ	ALL DIMS IN mm	DWG NO	49685	SHEET 1 OF 1