




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

SURFACE FLATNESS	2λ
PARALLELISM (arcmin)	≤ 3.5
CLEAR APERTURE (%)	≥ 90
EDGES	Chrome, Nickel, and Gold
WAVELENGTH RANGE (nm)	200 - 5500
WAVELENGTH RANGE (μm)	0.2 - 5.5
SOLDERABILITY	MIL-STD-883
RoHS	COMPLIANT

EO® **Edmund Optics**®



THIRD ANGLE
PROJECTION

TITLE

25mm Diameter Uncoated, Metalized
Sapphire Window

ALL DIMS IN

mm

DWG NO

66912

SHEET
1 OF 1