

NOTES:



- SUBSTRATE MATERIAL:  
NITROCELLULOSE
- COATING (APPLY ACROSS COATING APERTURE)

S1: NONE


8% R @ 400 - 2200nm @ 45° AOI  
92% T @ 400 - 2200nm @ 45° AOI  
R/T TOLERANCE: ±3%

S2: NONE

- ROHS : EXEMPT



SECTION A-A



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



REV.A.	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø76.20	Ø76.20
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

TITLE	BS PELLICLE 3in DIA 8R/92T		
DWG NO	39486	SHEET	1 OF 1