





NOTES:

1. SUBSTRATE: UV FUSED SILICA
2. ROHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
SURFACE QUALITY	80-50
CENTER WAVELENGTH (nm)	289
FULL WIDTH HALF MAX (FWHM) (nm)	10±2
MIN TRANSMISSION (%)	15
CLEAR APERTURE	Ø21.00
BEVEL	PROTECTIVE AS NEEDED

 **Edmund Optics®**

THIRD ANGLE PROJECTION 	TITLE	289nm, 10nm FWHM, 25mm DIA. FIRST SURFACE UV BANDPASS FILTER	
	ALL DIMS IN	mm	DWG NO
			SHEET 1 OF 1