





FOCAL LENGTH (EFL): 24 ±0,24  
BACK FOCAL LENGTH (BFL): 22,63

1 AR COATING: NONE

| LEFT SURFACE                                                                       |                          |             | MATERIAL                                                                            | RIGHT SURFACE                                                                                                 |                          |
|------------------------------------------------------------------------------------|--------------------------|-------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|--------------------------|
| R                                                                                  | 11,003±0,011 CX          |             | GLASS FUSED SILICA 458/678                                                          | R                                                                                                             | ∞ PL                     |
| Øe                                                                                 | 5,4                      |             |                                                                                     | Øe                                                                                                            | 5,4                      |
| 3/                                                                                 | 2 (0,2) λ=632,8 nm       |             |                                                                                     | 3/                                                                                                            | 2 (0,2) λ=632,8 nm       |
| 4/                                                                                 | -                        |             |                                                                                     | 4/                                                                                                            | 2,18'                    |
| 5/                                                                                 | 20 - 10 (MIL-PRF-13830B) |             |                                                                                     | 5/                                                                                                            | 20 - 10 (MIL-PRF-13830B) |
| 6/                                                                                 | -                        |             |                                                                                     | 6/                                                                                                            | -                        |
| PROTECTIVE CHAMFERS AS NEEDED                                                      |                          |             | FIRST ANGLE PROJECTION                                                              | <div> Edmund Optics®</div> |                          |
| ROHS:<br>COMPLIANT                                                                 | SCALE:<br>NONE           | λ = 587,6nm |                                                                                     |                                                                                                               |                          |
| SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY |                          |             |  | TITLE                                                                                                         |                          |
| FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING                     |                          |             |                                                                                     | 6mm Diameter x 24mm FL, 355nm Coated, Laser Grade PCX Lens                                                    |                          |
| INDICATIONS IN ACCORDANCE WITH ISO 10110                                           |                          |             | ALL DIMS IN:                                                                        | mm                                                                                                            | DWG NO                   |
|                                                                                    |                          |             |                                                                                     |                                                                                                               | 87934                    |
|                                                                                    |                          |             | SHEET SIZE                                                                          |                                                                                                               | SHEET                    |
|                                                                                    |                          |             | A4                                                                                  |                                                                                                               | 1 OF 1                   |