



NOTES:

1. TYPE OF MOVEMENT: Rotary
TRAVEL (°) : 360.00
ACCURACY (°) ± 0.02
2. TYPE OF DRIVE: Worm Gear
3. LOAD CAPACITY (kg): 2
4. RESOLUTION (arcsec): 6
5. MAXIMUM RUNOUT (μm): ± 2.5
6. PITCH: 80:1 worm drive
7. REPEATABILITY (μm): ± 2.5
8. GEAR DRIVE RATIO: 64:1
SPEED (°/s): 24
FINAL OUTPUT RATIO: 5120:1
9. VACUUM COMPATIBILITY: 10-3 Torr



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO
CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR
REFERENCE ONLY

Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	360° Travel, Micro Mini Stage, Rotary Type	
ALL DIMS IN	in	DWG NO	53672	SHEET 1 OF 1