



NOTES:


1. MATERIAL: PMMA
2. COATING (APPLY ACROSS CLEAR APERTURE):  
R(AVG) < 0.5% @ 700 - 1100nm
3. FOCAL LENGTH TOLERANCE: ±%1
4. RoHS: COMPLIANT



SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

		EFL: 50.80mm		 <b>Edmund Optics<sup>®</sup></b>	
		BFL: 49.00mm			
				TITLE	
				12.7mm DIA. f/4 NIR COATED, MOLDED ACRYLIC ASPHERIC LENS	
SHAPE	S1 CONVEX	S2 PLANO	ALL DIMS IN	mm	DWG NO
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			64582
					SHEET 1 OF 1