





FOCAL LENGTH (EFL): 250 ±2,5  
BACK FOCAL LENGTH (BFL): 247,36

| LEFT SURFACE                                                                       |                |           | MATERIAL                                                                            | RIGHT SURFACE                                               |                 |       |
|------------------------------------------------------------------------------------|----------------|-----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------|-----------------|-------|
| R 119,022 CX                                                                       |                |           | GLASS Fused Silica 458/678                                                          | R ∞ PL                                                      |                 |       |
| Øe 11,7                                                                            |                |           |                                                                                     | Øe 11,7                                                     |                 |       |
| ⌀ -                                                                                |                |           |                                                                                     | ⌀ -                                                         |                 |       |
| 3/ 2 (0,2) λ=632,8 nm                                                              |                |           |                                                                                     | 3/ 2 (0,2) λ=632,8 nm                                       |                 |       |
| 4/ -                                                                               |                |           |                                                                                     | 4/ 2,18'                                                    |                 |       |
| 5/ 10 - 5                                                                          |                |           |                                                                                     | 5/ 10 - 5                                                   |                 |       |
| 6/ -                                                                               |                |           | 6/ -                                                                                |                                                             |                 |       |
| PROTECTIVE CHAMFERS AS NEEDED                                                      |                |           | FIRST ANGLE PROJECTION                                                              | <div>EO<sup>®</sup> Edmund Optics<sup>®</sup></div>         |                 |       |
| ROHS:<br>COMPLIANT                                                                 | SCALE:<br>NONE | λ = 355nm |                                                                                     |                                                             |                 |       |
| SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY |                |           |  | TITLE<br>12,7mm Dia x 250mm FL, Uncoated, Plano-Convex Lens |                 |       |
| FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING                     |                |           |                                                                                     |                                                             |                 |       |
| INDICATIONS IN ACCORDANCE WITH ISO 10110                                           |                |           | ALL DIMS<br>IN:                                                                     | mm                                                          | DWG NO          | 38641 |
|                                                                                    |                |           |                                                                                     |                                                             | SHEET<br>SIZE   | A4    |
|                                                                                    |                |           |                                                                                     |                                                             | SHEET<br>1 OF 1 |       |