

NOTES:





1. SUBSTRATE: BOROFLOAT33
2. COATING

DURABILITY:
PHYSICAL: MIL-C-48497A, SECTION 3.4.1
ENVIRONMENTAL: MIL-STD-810F, SECTION 507.4

PERFORMANCE SPECIFICATIONS @ 0° AOI
T(AVG): ≥85% from 400 - 675nm
T(AVG): ≤1% from 730 - 900nm
CUT-OFF WAVELENGTH: T(ABS) = 50% @ 700nm ± 14nm

3. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SHORTPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø11.25	Ø11.25
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EO® **Edmund Optics**®



ALL DIMS IN mm

TITLE	FILTER OD2 SHORTPASS 700nm 12.5mm		
DWG NO	15250	SHEET 1 OF 1	