NOTES:

1. SUBSTRATE:


D263®Teco


2. COATING (APPLY ACROSS CLEAR APERTURE)


S1 & S2: NONE

3. FINE GRIND EDGES

4. ROHS COMPLIANT







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	80-50	80-50	
CLEAR APERTURE	Ø 22.50	Ø 22.50	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	

		Edmund Option		S®
THIRD ANGLE _ PROJECTION		TITLE	25mm Dia., 0.4mm Thick, SCHOTT D263® T eco Window	
ALL DIMS IN	mm	DWG NO	18299	SHEET 1 OF 1