

NOTES:



1. SUBSTRATE: B270

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1&S2: R(AVG) ≤1.50% @ 632.8nm (N-BK7)

3. FINE GRIND SURFACE


4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø 11.25	Ø 11.25
SURFACE FLATNESS	1λ	1λ
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm



TITLE: 12.5mm Dia., 1mm Thick, MgF2 Coated, B270 Window

DWG NO: 17173

SHEET 1 OF 1