





NOTES:

1. SUBSTRATE: COLORED GLASS



BANDPASS FILTER

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH (nm)	390.00
FULL WIDTH HALF MAX (FWHM) (nm)	125.00
SURFACE QUALITY	60-40
COATING TYPE	UNCOATED
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION

ALL DIMS IN

mm

Edmund Optics®

TITLE	Hoya B390 (UVVIS) 25.4mm Dia., 1mm Thick, Colored Glass Bandpass Filter		
DWG NO	18782	SHEET 1 OF 1	