



- NOTES:
- 1. SUBSTRATE: N-BK7
  - 2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
  - 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: VIS 0° (425-675nm)  
S2: VIS 0° (425-675nm)  
Ravg ≤0.4% @ 425 - 675nm

4. FINE GRIND SURFACE

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	$\phi 9.00$	$\phi 9.00$
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN mm

**Edmund Optics®**

TITLE

10mm Dia., 1mm Thick, VIS 0° Coated  $\lambda/4$   
N-BK7 Window

DWG NO

23379

SHEET  
17 OF 84