



NOTES:

1. SUBSTRATE MATERIAL: N-BK7
2. ROHS COMPLIANT
3. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: NONE
 - S2: Ravg >89% @ 250 - 450nm
 - Ravg >85% @ 250 - 700nm

4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
ANGEL TOL. (arcmin)	±2	±2
SURFACE QUALITY	40-20	40-20
SURFACE FLATNESS	λ/4	λ/4
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE: 15mm, UV Enhanced Aluminum, N-BK7 90° Specialty Mirror

DWG NO: 25-709

SHEET 24 OF 31