





$f'$ : -200 ±2

BACK FOCAL LENGTH (BFL): -201,71



| LEFT SURFACE                                                                                                                                                                                                                                                                                                                                           |  |  | MATERIAL                                                | RIGHT SURFACE                                                                                                                                                                                                    |               |  |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|---------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|--|
| R 91,692 CV<br><br>Øe 24<br><br>⌂ AR Rave(250nm - 700nm, 0°) ≤ 1,50%<br>R(350nm - 450nm, 0°) ≤ 1,00%<br><br>3/ 3 (0,5) λ=632,8 nm<br><br>4/ 2,18'<br><br>5/ 40 - 20<br><br>6/ -<br><br><div><div></div><div>P</div></div>                                                                                                                              |  |  | GLASS<br>Fused Silica<br>458/678<br>Nd: 1,458           | R ∞ PL<br><br>Øe 24<br><br>⌂ AR Rave(250nm - 700nm, 0°) ≤ 1,50%<br>R(350nm - 450nm, 0°) ≤ 1,00%<br><br>3/ 3 (0,5) λ=632,8 nm<br><br>4/ -<br><br>5/ 40 - 20<br><br>6/ -<br><br><div><div></div><div>P</div></div> |               |  |
| PROTECTIVE CHAMFERS AS NEEDED<br><div><div>ROHS:<br/>COMPLIANT</div><div>SCALE:<br/>NONE</div><div>λ = 587,6nm</div></div> <div>SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY</div> <div>FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING</div> <div>INDICATIONS IN ACCORDANCE WITH ISO 10110</div> |  |  |                                                         | Edmund Optics®                                                                                                                                                                                                   |               |  |
| <div><div></div><div>⊕</div></div>                                                                                                                                                                                                                                                                                                                     |  |  | 25mm Dia x -200mm FL, UV-VIS Coated, Plano-Concave Lens |                                                                                                                                                                                                                  |               |  |
| ALL DIMS IN: mm                                                                                                                                                                                                                                                                                                                                        |  |  | TITLE                                                   |                                                                                                                                                                                                                  |               |  |
|                                                                                                                                                                                                                                                                                                                                                        |  |  | DWG NO                                                  |                                                                                                                                                                                                                  |               |  |
|                                                                                                                                                                                                                                                                                                                                                        |  |  | 71106                                                   |                                                                                                                                                                                                                  | SHEET SIZE A4 |  |
|                                                                                                                                                                                                                                                                                                                                                        |  |  |                                                         |                                                                                                                                                                                                                  | SHEET 1 OF 1  |  |