

[All Products](#) / [Optomechanics | 光機組件](#) / [Irises and Apertures | 光圈類](#) / [Pinholes and Slits | 針孔和狹縫](#)

Acktar 黑化狹縫

See More by [Acktar](#)



- 寬頻帶低反射鍍膜
- 99% 吸收率, 涵蓋 EUV 至 SWIR
- 狹縫尺寸最小 25µm x 3mm
- 提供未裝框及已裝框版本

一般規格

物理和機械特性

Construction: Stainless Steel

Slit Length (mm): 3.0

光學特性

Coating: Magic Black™

材料特性

Absorbance (%): 99

Technical Information

產品

Type	Outer Diameter (mm)	Construction	Slit Length (mm)	Slit Width (μm)	庫存號碼	價格	Buy
Unmounted	9.53	Stainless Steel	3.0	25	#12-176	NT\$6,633 Volume Pricing	2 庫存
Unmounted	9.53	Stainless Steel	3.0	50	#12-177	NT\$6,633 Volume Pricing	3 庫存
Unmounted	9.53	Stainless Steel	3.0	75	#17-462	NT\$6,633 Volume Pricing	1 庫存
Unmounted	9.53	Stainless Steel	3.0	100	#12-178	NT\$6,633 Volume Pricing	4 庫存
Unmounted	9.53	Stainless Steel	3.0	150	#17-463	NT\$6,633 Volume Pricing	2 庫存
Unmounted	9.53	Stainless Steel	3.0	200	#12-179	NT\$6,633 Volume Pricing	3 庫存
Unmounted	9.53	Stainless Steel	3.0	500	#17-464	NT\$6,633 Volume Pricing	17 庫存
Unmounted	9.53	Stainless Steel	3.0	1000	#17-465	NT\$6,633 Volume Pricing	14 庫存
Mounted	25.0	Stainless Steel	3.0	25	#12-180	NT\$6,994 Volume Pricing	4 庫存
Mounted	25.0	Stainless Steel	3.0	50	#12-181	NT\$6,994 Volume Pricing	1 庫存
Mounted	25.0	Stainless Steel	3.0	75	#17-466	NT\$6,994 Volume Pricing	1 庫存
Mounted	25.0	Stainless Steel	3.0	100	#12-182	NT\$6,994 Volume Pricing	1 庫存
Mounted	25.0	Stainless Steel	3.0	150	#17-467	NT\$6,994 Volume Pricing	2 庫存
Mounted	25.0	Stainless Steel	3.0	200	#12-183	NT\$6,994 Volume Pricing	4 庫存
Mounted	25.0	Stainless Steel	3.0	500	#17-468	NT\$6,994 Volume Pricing	3 庫存
Mounted	25.0	Stainless Steel	3.0	1000	#17-469	NT\$6,994 Volume Pricing	1 庫存



Copyright 2023, Edmund Optics Inc., 14F., No.83, Sec. 4, Wenxin Road, Beitun District , Taichung City 406, Taiwan (R.O.C.)

電話: 1-800-363-1992 :

www.edmundoptics.com