

[All Products](#) / [Cameras | 相機](#) / [High Speed Interface Cameras | 高速接口相機](#)

Basler Boost CoaXPress 2.0 相機套件 See More by [Basler](#)

- 充分利用傳感器高分辨率和高速性能
- 高寬頻CoaXPress 2.0 (CXP-12) 相機
- 相機隨附CXP-12介面卡1C



一般規格
概況

Manufacturer:	Basler	Camera Series:	boost
Note:	Kit includes a camera, CXP-12 interface card, CXP data cable, 2 heat sinks, an I/O cable, and C-Mount Lens adapter (adapter is required to attach lens)		

物理和機械特性

Dimensions (mm):	45 x 80 x 80 (includes connectors and lens mount)		
Weight (g):	180	Housing:	Full

傳感器

Image Buffer:	Not Specified	Pixel Size, H x V (µm):	3.45 x 3.45
Type of Sensor:	Progressive Scan CMOS	Shutter Type:	Global
Pixel Depth:	8 bit	Exposure Time:	Programmable via camera API, hardware trigger
Dynamic Range (dB):	Not Specified	Machine Vision Standard:	CoaXPress 2.0, GenICam

電氣性能

Power Consumption (W):	9.6
------------------------	-----

硬體與介面連接

Interface:	CoaXPress 2.0 (CXP-12)		
Connector:	CoaXPress, Micro-BNC	Power Supply:	Power over CoaXPress or via GPIO
GPIOs:	1 opto-coupled input, 2 GPIO	Synchronization:	Hardware Trigger (GPIO), Software Trigger, or Free-Run
Interface Port Orientation:	Back Panel	GPIO Connector Type:	6-pin M7
Operating System:	Software Driver: Windows		

螺紋和安裝

Mount:	C-Mount
Mounting Threads:	1/4-20 (Integrated into Housing)

環境和耐用性因素

Operating Temperature (°C):	0 to +50
Storage Temperature (°C):	-20 to +80

Technical Information

產品

Type	Model Number	Sensor Format	Resolution (Megapixels)	Connector	Mount	庫存號碼	價格	Buy
Monochrome Camera	boA4112-68cm	1.1"	12.30	CoaXPress, Micro-BNC	C-Mount	#14-255	NT\$147,350	聯絡我們
Color Camera	boA4112-68cc	1.1"	12.30	CoaXPress, Micro-BNC	C-Mount	#14-256	NT\$149,625	聯絡我們
Monochrome Camera	boA4096-93cm	1"	8.90	CoaXPress, Micro-BNC	C-Mount	#14-257	NT\$137,725	聯絡我們



Copyright 2023, Edmund Optics Inc., 14F., No.83, Sec. 4, Wenxin Road, Beitun District , Taichung City 406, Taiwan (R.O.C.)
電話: 1-800-363-1992 :
www.edmundoptics.com