

[All Products](#) / [Optomechanics | 光機組件](#) / [Motorized Translation Stages | 電動移動平臺](#) / [Motorized Rotary Stages](#)

緊湊型電動旋轉台



- 緊湊的機構尺寸和經濟的價格
- 輕巧的外殼和耐用的調整台
- 可相容 [TECHSPEC 調整台](#)
- 使用電源 [#21-075](#) 為控制器 [#23-931](#) 供電

一般規格

概況

Note:		Controller Required: #23-931		Type of Motor:	Stepper Motor
物理和機械特性					
Type of Movement:		Rotary		Guide System:	Ball Bearing
Travel (°):		360		Accuracy (°):	0.03
Backlash (°):		0.2		Construction:	Aluminum, 3D Printed Plastic
Height (mm):		44.7		Load Capacity (kg):	0.5
Repeatability (°):		0.03		Speed (°/s):	240
Weight (kg):		0.25		Table Diameter (mm):	70
Parallelism (°):		0.0083		Min. Incremental Movement (°):	0.02
光學特性					
Resolution (μm):				0.02°	
電氣性能					
Maximum Operating Current (mA):				500	
硬體與介面連接					
Type of Drive:		Gear Transmission		Computer Interface:	USB-C
環境和耐用性因素					
Operating Temperature (°C):				10-40	

Technical Information

產品

Table Diameter (mm)	Type	Travel (°)	庫存號碼	價格	Buy
70	Metric	360	#23-929	NT\$32,806	4 庫存
70	English	360	#23-930	NT\$32,806	2 庫存



Copyright 2023, Edmund Optics Inc., 14F., No.83, Sec. 4, Wenxin Road, Beitun District , Taichung City 406, Taiwan (R.O.C.)

電話: 1-800-363-1992 :

www.edmundoptics.com