

[All Products](#) / [Optics | 光學產品](#) / [Beamsplitters | 分光鏡](#) / [Cube Beamsplitters | 立體分光鏡](#)

雷射光高能量偏振立方體分光鏡



- 採用光學接觸設計，以提升損傷閾值
- P偏振光的穿透率超過96%
- 具有超過1000:1的高消光比

一般規格

物理和機械特性

Clear Aperture (%): 90

Construction: Cube

光學特性

Extinction Ratio: 1000:1

Substrate: [Fused Silica](#) (Corning 7980)

Surface Flatness (P-V): $\lambda/6$

Surface Quality: 40-20

Damage Threshold, By Design: Typical: 20 J/cm² @ 1064nm 10ns, 20Hz

Technical Information

產品

Extinction Ratio	Dimensions (mm)	Wavelength Range (nm)	DWL (nm)	庫存號碼	價格	Buy
1000:1	12.7 x 12.7 x 12.7	345 - 365	355	#88-232	NT\$29,741 Volume Pricing	2 庫存
1000:1	12.7 x 12.7 x 12.7	395 - 415	405	#71-024	NT\$28,840 Volume Pricing	聯絡我們
1000:1	12.7 x 12.7 x 12.7	510 - 550	532	#88-233	NT\$28,840 Volume Pricing	聯絡我們
1000:1	12.7 x 12.7 x 12.7	735 - 775	755	#71-027	NT\$28,840 Volume Pricing	8 庫存
1000:1	12.7 x 12.7 x 12.7	1020 - 1090	1064	#88-234	NT\$28,840 Volume Pricing	聯絡我們
1000:1	12.7 x 12.7 x 12.7	1520 - 1550	1550	#71-029	NT\$28,840 Volume Pricing	5 庫存
1000:1	25.4 x 25.4 x 25.4	345 - 365	355	#33-317	NT\$42,719 Volume Pricing	2 庫存
1000:1	25.4 x 25.4 x 25.4	395 - 415	405	#71-025	NT\$41,818 Volume Pricing	3 庫存
1000:1	25.4 x 25.4 x 25.4	510 - 550	532	#33-318	NT\$41,818 Volume Pricing	3 庫存
1000:1	25.4 x 25.4 x 25.4	735 - 775	755	#71-028	NT\$41,818 Volume Pricing	9 庫存
1000:1	25.4 x 25.4 x 25.4	1020 - 1090	1064	#33-319	NT\$41,818 Volume Pricing	聯絡我們
1000:1	25.4 x 25.4 x 25.4	1520 - 1550	1550	#71-030	NT\$41,818 Volume Pricing	4 庫存



Copyright 2023, Edmund Optics Inc., 14F., No.83, Sec. 4, Wenxin Road, Beitun District, Taichung City 406, Taiwan (R.O.C.)
 電話: 1-800-363-1992 :
www.edmundoptics.com