NOTES:

- 1. SUBSTRATE: N-BK7
- 2. CENTERING TOLERANCE (AT 587.6nm): BEAM DEVIATION: ≤2 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE):


VIS S1, S2, S3, & S4: R(AVG) <0.5% @ 430 - 670nm S5: MULTILAYER DIELECTRIC TO ACHIEVE: TRANSMISSION > 45% ± 5% POLARIZATION < 6%

4. FINE GROUND SURFACE

ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE NOA 61

6. MARK IDENTIFIES BEAMSPLITTED COATED RIGHT ANGLE PRISM





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2				Edmund Option	CS®
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION		TITLE	50mm VIS, Non-Polarizing Cube Beamsplitter	
SURFACE ACCURACY	1/8 WAVE	1/8 WAVE					
SURFACE QUALITY	40-20	40-20		1			CHEET
CLEAR APERTURE	> 90%	> 90%	ALL DIMS IN	mm	DWG NO	49004	SHEET 1 OF 1