

NOTES:

1. SUBSTRATE:  
ELEMENT A: N-SK14  
ELEMENT B: N-SF57

2. CENTERING: 3-5 ARCMIN

3. COATING:

S1: R(AVG) ≤ 0.4% FROM 425-675nm @ 0° AOI

S2, S3, & S4: NONE

4. FINE GRIND SURFACE

5. ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE  
NOA 61



6. POLYMER ASPHERE APPLIED TO S4 OF ACHROMAT:

MATERIAL:  $n_d=1.517$ ,  $V_d=52.0$

CENTER THICKNESS: 0.060mm ADDED TO S4

CLEAR APERTURE(CENTERED ON S4 WITH NO MACRO DEFECTS):

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS})^2 * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



COEFFICIENT TABLE 6.

| COEFFICIENT   | S4            |
|---------------|---------------|
| SEMI-DIAMETER | 1.175000E+01  |
| (1/RADIUS)    | -0.977163E-02 |
| k             | 0.000000E+00  |
| D             | 0.000000E+00  |
| E             | 9.577981E-06  |
| F             | -1.436447E-08 |
| G             | 0.000000E+00  |
| H             | 0.000000E+00  |
| J             | 0.000000E+00  |
| L             | 0.000000E+00  |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                    | S1                   | S2                   | S3                   | S4                   |
|--------------------|----------------------|----------------------|----------------------|----------------------|
| SHAPE              | CONVEX               | CONVEX               | CONCAVE              | CONVEX               |
| RADIUS             | 24.80                | 37.60                | 37.60                | 102.34 6.            |
| SURFACE QUALITY    | 60-40                | 60-40                | 60-40                | 80-50                |
| MIN CLEAR APERTURE | Ø22.25               | Ø22.25               | Ø22.25               | Ø23.00               |
| BEVEL MAX FACE     | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

EFL: 40.00mm

BFL: 33.48mm



ALL DIMS IN

mm



Edmund Optics®

TITLE

25mm DIAMETER x 40mm EFL ASPHERIZED  
ACHROMATIC LENS

DWG NO

49664

SHEET  
1 OF 1

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**