


NOTES:

1. SUBSTRATE MATERIAL: GRADE A FINE ANNEALED
SCHOTT: BOROFLOAT® 472/657
2. COATING(APPLY ACROSS CLEAR APERTURE)
SPECIFICATIONS APPLY FOR 0° AOI

S1: T(AVG) > 90% FROM 400-690nm
R(AVG) > 95% FROM 710-1150nm

S2: R(AVG) < 1.0% FROM 400-700nm
3. EDGES: CUT, SHARP EDGES REMOVED



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

			EFL (AT 587.6nm)	NA	EOL [®] Edmund Optics [®]		
	S1	S2					
SHAPE	PLANO	PLANO					
SURFACE ACCURACY AT 632.8nm (P-V)	4-6 WAVES PER INCH	4-6 WAVES PER INCH	BFL (AT 587.6nm)	NA	TITLE	0° AOI, 101 x 127mm, Hot Mirror	
SURFACE QUALITY	80 - 50	80 - 50					
MIN CLEAR APERTURE	100.00 x 126.00	100.00 x 126.00	ALL DIMS IN	mm	DWG NO	64462	SHEET 1 OF 1