

NOTES:

- SUBSTRATE MATERIAL:
 OPTICAL GRADE GERMANIUM
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 WITHIN 1 ARCMIN
- 3. COATING(APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) < 3% FROM 3.0 TO 5.0 µm
- 4. FINE GROUND SURFACE
- 5. PROTECTIVE BEVEL AS NEEDED





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2				Edmund Option	CS®
SHAPE	PLANO	PLANO			TITLE	30mm Dia. x 3.0mm Thick 3-5µm AR Coating, Ge Window	
SURFACE ACCURACY AT 10.6µm (P-V)	1/10 WAVE	1/10 WAVE					
SURFACE QUALITY	60 - 40	60 - 40				CUEFT	
MIN CLEAR APERTURE	Ø27.0	Ø 27.0	ALL DIMS IN	mm	DWG NO	89566	SHEET 1 OF 1