


NOTES:

1. SUBSTRATE: IG6 (As40Se60)
2. COATING
S1: NONE
S2: NONE
3. EDGES: DIAMOND TURNED
4. CENTERING: 3-5 arcmin
5. RoHS: COMPLIANT
6. ASPHERIC SURFACE DESCRIBED BY THE FOLLOWING EQUATION AND COEFFICIENTS SHOWN IN TABLE BELOW



$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1 + k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



COEFFICIENT TABLE	
COEFFICIENT	S1
k	0.000000E+00
D	0.000000E+00
E	-1.0610728E-5
F	1.2693411E-8
G	-1.188073E-13
H	-1.5816012E-11
J	1.0815338E-14
L	0.000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	CONVEX	CONCAVE	EFL @ 4000nm: 50	 Edmund Optics®		
RADIUS	46.200	∞	BFL @ 4000nm: 44.2			
SURFACE ACCURACY	0.3µm	N/A		TITLE IG6 ASPHERIC LENS 50mm DIA. X 50mm, UNCOATED		
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	90%	90%				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	88263
					SHEET 1 OF 1	