


TECHSPEC® Achromatic Lenses


TECHSPEC® ACHROMATIC LENSES

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy



+ 0.4861
x 0.5876
□ 0.6563





49323 TUE DEC 16 2008 UNITS ARE μm . FIELD RMS RADIUS : 16.502 GEO RADIUS : 47.267 SCALE BAR : 100	SPOT DIAGRAM
	EDMUND OPTICS HTTP://WWW.EDMONDOPTICS.COM

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://WWW.EDMONDOPTICS.COM)

CHROMATIC FOCAL SHIFT

49323 TUE DEC 16 2008 MAXIMUM FOCAL SHIFT RANGE: 247.8483 μm DIFFRACTION LIMITED RANGE: 9.377 μm PUPIL ZONE: 0.0000	EDMUND OPTICS HTTP://WWW.EDMONDOPTICS.COM
---	--



49323 TUE DEC 16 2008 MAXIMUM SCALE: ± 200.000 μm . 0.486 0.588 0.656	EDMUND OPTICS HTTP://WWW.EDMONDOPTICS.COM
---	--

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://WWW.EDMONDOPTICS.COM)

49323 TUE DEC 16 2008 DATA FOR 0.4000 TO 1.0000 μm . SURFACE: IMAGE	EDMUND OPTICS HTTP://WWW.EDMONDOPTICS.COM
---	--