



TECHSPEC® Achromatic Lenses

TECHSPEC® ACHROMATIC LENSES

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy



SPOT DIAGRAM

OBJ: 0.000 DEG



49323INK
TUE DEC 16 2008 UNITS ARE μm.
FIELD : 16.562
RMS RADIUS : 47.267
GEO RADIUS : 100
SCALE BAR : 100

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://www.edmundoptics.com)

CHROMATIC FOCAL SHIFT

49323INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 247.8483 μm
DIFFRACTION LIMITED RANGE: 9.377 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://www.edmundoptics.com)



49323INK
TUE DEC 16 2008
MAXIMUM SCALE: ± 200.000 μm.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://www.edmundoptics.com)

49323INK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm.
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://www.edmundoptics.com)