

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

NOTES:

1. SUBSTRATE
UV GRADE FUSED SILICA
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 ARCSEC
3. COATING (APPLY ACROSS COATING APERTURE)


PERFORMANCE SPECIFICATIONS @ 0° AOI
T(AVG): >85% FROM 1110 - 2000nm
T(AVG): < 1% FROM 820 - 1025nm
T(ABS): = 50% @ 1075nm

S1: MULTILAYER DIELECTRIC COATING
S2: SINGLE LAYER MgF2


4. FINE GRIND SURFACE

5. TRANSMITTED WAVEFRONT DISTORTION RMS@ 632.8nm ≤ ¼ WAVE

6. ROHS COMPLIANT



LONGPASS FILTER




SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	80%	80%
COATING APERTURE	Ø20.00	Ø20.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

Edmund Optics®

THIRD ANGLE
PROJECTION



TITLE

OD2, Ø25mm, 1075nm LONGPASS FILTER

DWG NO

64688

SHEET
1 OF 1

ALL DIMS IN

mm