



NOTES:

1. SUBSTRATE:
Schott KG-5
2. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: NONE

3. FINE GRIND SURFACE

4. WAVELENGTH RANGE: 300 - 2700 nm
5. DENSITY (g/cm³): 2.53
OPERATING TEMPERATURE (°C): 300 Maximum
REFLECTION FACTOR: 0.92
6. ROHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

| | | | | | | | |
|-----------------|---------------------|---------------------|------------------------|----|--------|--|--------------|
| | S1 | S2 | THIRD ANGLE PROJECTION | | TITLE | 50mm Dia. SCHOTT KG-5 Heat Absorbing Glass | |
| SHAPE | PLANO | PLANO | ALL DIMS IN | mm | DWG NO | 49095 | SHEET 1 OF 1 |
| SURFACE QUALITY | 60-40 | 60-40 | | | | | |
| BEVEL | PROTECTED AS NEEDED | PROTECTED AS NEEDED | | | | | |