


NOTES:



1. SUBSTRATE
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 arcsec
3. COATING (APPLY ACROSS COATING APERTURE)
ENVIRONMENTAL DURABILITY:
PHYSICAL DURABILITY:
PERFORMANCE SPECIFICATIONS:
T(avg): >85% FROM 880 - 1600nm FOR RANDOM POLARIZATION @ 45° AOI
T(abs): >80% FROM 880 - 1600nm FOR ALL POLARIZATIONS @ 45° AOI
R(avg): >97% FROM 635 - 805nm FOR RANDOM POLARIZATION @ 45° AOI
R(abs): >95% FROM 635 - 805nm FOR ALL POLARIZATIONS @ 45° AOI
T(abs): = 50% 850nm @ 45° AOI

4. FINE GRIND SURFACE



5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS
APPLY ACROSS CLEAR APERTURE
6. TRANSMITTED WAVEFRONT DISTORTION RMS@ 632.8nm $\leq \frac{1}{4} \lambda$
7. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO		TITLE	25.2 x 35.6mm, 850nm DICHROIC LONGPASS FILTER	
SURFACE QUALITY	60-40	60-40		DWG NO	69906	SHEET 1 OF 1
CLEAR APERTURE	22.0 x 32.0	22.0 x 32.0				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm		