




NOTES:

1. SUBSTRATE:  
Schott KG-5
2. COATING (APPLY ACROSS COATING APERTURE)  
S1 & S2: NONE



3. FINE GRIND SURFACE

4. WAVELENGTH RANGE: 300 - 2700 nm
5. DENSITY (g/cm<sup>3</sup>): 2.53  
OPERATING TEMPERATURE (°C): 300 Maximum  
REFLECTION FACTOR: 0.92
6. ROHS: COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	25 x 25mm SCHOTT KG-5 Heat Absorbing Glass	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	49094	SHEET 1 OF 1
SURFACE QUALITY	60-40	60-40					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					