



TECHSPEC® ACHROMATIC LENSES

TECHSPEC® ACHROMATIC LENSES



Surface: IMA

Spot Diagram

49941
 4/24/2017
 Units are μm.
 Field : 1
 RMS radius : 64.721
 GEO radius : 157.196
 Scale bar : 400
 Airy Radius: 1.031 μm. Legend items refer to Wavelengths
 Reference : Chief Ray

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49941.ZMX
 Configuration 1 of 1



Chromatic Focal Shift

49941
 4/24/2017
 Maximum Focal Shift Range: 65.7345 μm
 Diffraction Limited Range: 4.858 μm
 Pupil Zone: 0.0000

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49941.ZMX
 Configuration 1 of 1

OBJ: 0.0000 (deg)



Legend:
 — Diff. Limit-Tangential —•• Diff. Limit-Sagittal
 — 0.0000 (deg)-Tangential —•• 0.0000 (deg)-Sagittal

Transverse Ray Fan Plot

49941
 4/24/2017
 Maximum Scale: ± 200.000 μm.
 0.486 0.588 0.656
 Surface: Image

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49941.ZMX
 Configuration 1 of 1

Polychromatic Diffraction MTF

49941
 4/24/2017
 Data for 0.4861 to 0.6563 μm.
 Surface: Image

Legend items refer to Field positions

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49941.ZMX
 Configuration 1 of 1