## NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. BEAM DEVIATION: ±3 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


\$1, \$2, \$3 & \$4: R(abs) <0.25% @ 632.8nm \$5: Tp/Ts >1000:1 @ 632.8nm TRANSMISSION >95% REFLECTION >99.5%

4. FINE GROUND SURFACE

 $\sqrt{5.}$  ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE 61

6. PROTECTIVE BEVEL AS NEEDED

7. MARK IDENTIFIES BEAMSPLITTER COATING RIGHT ANGLE PRISM



## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1, \$2, \$3, \$4	\$5	]			Edmund Optics®	)
SHAPE	PLANO	PLANO				5 mm, 632.8nm, LASER LINE POLARIZING CUB	
SURFACE FLATNESS	λ/4	λ/4	THIRD ANGLE PROJECTION		TITLE	BEAMSPLITTER	, L
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	90	90	ALL DIMS IN	mm	DWG NO	47776 SHE 1 O	