



NOTES:

- 1. SUBSTRATE:
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)
S1: Aluminum w/ Protective Overcoat
R(AVG)>85% FROM 400-700nm, @ 45° AOI

S2: NONE

3. FINE GRIND SURFACE

4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	4.07 x 2.88	2.88 x 2.88
COATING APERTURE	4.07 x 2.88	2.88 x 2.88
SURFACE FLATNESS	λ/8	λ/8
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN

mm

TITLE	3.2mm, Aluminum Coated, N-BK7 High Tolerance RA Prism		
DWG NO	32538	SHEET 1 OF 1	