




NOTES:

1. SUBSTRATE MATERIAL:  
BOROFLOAT®
2. CLEAR APERTURE AND COATING APERTURE  
ARE CENTERED ON SURFACES
3. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: R(avg)>95 @ 750-1150nm  
T(avg)>90 @ 425-675nm  
  
S2:NONE



4. FINE GRIND SURFACE


5. POWER, IRREGULARITY, AND SURFACE QUALITY  
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE FLATNESS	4 - 6λ	4 - 6λ
CLEAR APERTURE	17.0 x 17.0	17.0 x 17.0
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



**EO**® **Edmund Optics**®

TITLE	20.0 x 20.0mm, 0° AOI, Hot Mirror		
DWG NO	62627	SHEET	1 OF 1