



# TECHSPEC® ACHROMATIC LENSES

TECHSPEC® ACHROMATIC LENSES



Surface: IMA

IMA: 0.000 mm

Spot Diagram

33920  
 4/21/2017  
 Units are μm. Airy Radius: 0.978 μm.  
 Field : 1  
 RMS radius : 161.051  
 GEO radius : 395.386  
 Scale bar : 1000

Reference : Chief Ray

Edmund Optics  
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



33920.ZMX  
 Configuration 1 of 1

Chromatic Focal Shift

33920  
 4/21/2017  
 Maximum Focal Shift Range: 116.9263 μm  
 Diffraction Limited Range: 4.375 μm  
 Pupil Zone: 0.0000

Edmund Optics  
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

33920.ZMX  
 Configuration 1 of 1



Legend items refer to Field positions

Transverse Ray Fan Plot

33920  
 4/21/2017  
 Maximum Scale: ± 500.000 μm.  
 0.486 0.588 0.656  
 Surface: Image

Edmund Optics  
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

33920.ZMX  
 Configuration 1 of 1

Polychromatic Diffraction MTF

33920  
 4/21/2017  
 Data for 0.4861 to 0.6563 μm.  
 Surface: Image

Legend items refer to Field positions

Edmund Optics  
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

33920.ZMX  
 Configuration 1 of 1