



TECHSPEC® ACHROMATIC LENSES





- 0.486133
- 0.587562
- 0.656273



Surface: IMA

Spot Diagram		Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM
33922 4/24/2017 Units are μm . Field : 1 RMS radius : 119.796 GEO radius : 302.485 Scale bar : 1000 Reference : Chief Ray	Airy Radius: 1.465 μm . Legend items refer to Wavelengths	33922.ZMX Configuration 1 of 1

Chromatic Focal Shift		Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM
33922 4/24/2017 Maximum Focal Shift Range: 339.9297 μm Diffraction Limited Range: 9.815 μm Pupil Zone: 0.0000	33922.ZMX Configuration 1 of 1	



- Diff. Limit-Tangential
- Diff. Limit-Sagittal
- 0.0000 (deg)-Tangential
- 0.0000 (deg)-Sagittal

Transverse Ray Fan Plot			Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM
33922 4/24/2017 Maximum Scale: $\pm 500.000 \mu\text{m}$. 0.486 0.588 0.656			33922.ZMX Configuration 1 of 1

Polychromatic Diffraction MTF			Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM
33922 4/24/2017 Data for 0.4861 to 0.6563 μm . Surface: Image	Legend items refer to Field positions	33922.ZMX Configuration 1 of 1	



Edmund
optics | worldwide

www.edmundoptics.com