



TECHSPEC® ACHROMATIC LENSES

TECHSPEC® ACHROMATIC LENSES



Surface: IMA

Spot Diagram

49278INK
 4/24/2017
 Units are μm .
 Field : 1
 RMS radius : 0.818
 GEO radius : 1.748
 Scale bar : 10
 Airy Radius: 3.182 μm . Legend items refer to Wavelengths
 Reference : Chief Ray

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49278INK.ZMX
 Configuration 1 of 1



Chromatic Focal Shift

49278INK
 4/24/2017
 Maximum Focal Shift Range: 31.2164 μm
 Diffraction Limited Range: 46.302 μm
 Pupil Zone: 0.0000

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49278INK.ZMX
 Configuration 1 of 1

OBJ: 0.0000 (deg)



—Diff. Limit-Tangential —Diff. Limit-Sagittal —0.0000 (deg)-Tangential —0.0000 (deg)-Sagittal

Transverse Ray Fan Plot

49278INK
 4/24/2017
 Maximum Scale: $\pm 2.000 \mu\text{m}$.
 0.486 0.588 0.656
 Surface: Image

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49278INK.ZMX
 Configuration 1 of 1

Polychromatic Diffraction MTF

49278INK
 4/24/2017
 Data for 0.4861 to 0.6563 μm .
 Surface: Image

Legend items refer to Field positions

Edmund Optics
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49278INK.ZMX
 Configuration 1 of 1