NOTES:

1. SUBSTRATE MATERIAL:

N-BK7

2. SURFACE \$1 TO BE PARALLEL WITH SURFACE \$2 TO WITHIN ≤3 ARCMIN

3. COATING (APPLY ACROSS CLEAR APERTURE)


S1: 80% R ±5% @ 550nm 20% T ±5% @ 550nm


S2: AR R(avg) ≤1%, R(abs) ≤2% @ 700 - 1100nm

4.

CUT WITH 0.25mm MAXIMUM EDGE CHIP

5. ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2
SHAPE	PLANO	PLANO
ANGLE OF INCIDENCE	45°	45°
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm

	B	Edmund Optics®
**************************************		25 x 25mm 80 R/20 T PLATE BEAMSPLITTER

THIRD ANGLE _ PROJECTION	\rightarrow	TITLE	25 x 25mm, 80 R/20 T, PLATE BEAMSPLITTER	
ALL DIMS IN	mm	DWG NO	68424	SHEET 1 OF 1